

AGILA TWIN

2970DIK075P50 OFFSET-31,4 AXLE-M8

EAN 4031582302677
Order number 00004821



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ● ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila twin |
| Housing type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 220.46 lb |
| Load capacity Static | 440.92 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 185 °F |
| Overall height | 4.02 in |
| Overall width | 2.8 in |
| Overall weight | 1.92 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Sheet Steel |
| Tread material | Solid rubber, non-marking |
| Bearing | Cone ball bearing |
| Wheel color | Blue passivated |
| Threadguards | With threadguard |
| Diameter | 2.95 in |
| Tread width | 0.98 in |
| Body width | 0.98 in |
| Hardness of tread (A) | 80 Shore A |

HOUSING

| | |
|---------------------|---------------------|
| Material | Steel sheet, medium |
| Fork shape | Twin wheel housing |
| Swivel bearing | Two ball races |
| Color | Blue passivated |
| Offset | 1.24 in |
| Swivel radius | 2.85 in |
| Swivel interference | 5.71 in |
| Dome diameter | 2.56 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 3.03 in |
| Plate width | 2.64 in |
| Plate hole length (Minimum) | 1.83 in |
| Plate hole length (Maximum) | 2.03 in |
| Plate hole width (Minimum) | 2.2 in |
| Plate hole width (Maximum) | 2.42 in |
| Plate hole diameter | 0.33 in |

AGILA TWIN

2970DIK075P50 OFFSET-31,4 AXLE-M8

EAN 4031582302677
Order number 00004821



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

