

STORA

2370DIK075P30-10,3

EAN 4031582300291
Order number 00004832



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	121.25 lb
Load capacity Static	242.51 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	3.94 in
Overall width	1.97 in
Overall weight	0.91 lb

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Wheel color	Blue passivated
Threadguards	With threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Color	Blue passivated
Offset	1.18 in
Swivel radius	2.66 in
Swivel interference	5.31 in
Dome diameter	1.71 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.41 in

STORA

2370DIK075P30-10,3

EAN 4031582300291
Order number 00004832



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

