

# ALPHA LIGHT

3430POO065P60-95X70

EAN 4031582303339  
Order number 10000285



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha light
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	120 kg
Load capacity Static	240 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	83 mm
Overall width	65 mm
Overall weight	0.401 kg

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	65 mm
Tread width	30 mm
Body width	30 mm
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	One ball race
Colour	Blue passivated
Offset	22 mm
Swivel radius	54.5 mm
Swivel interference	109 mm
Dome diameter	65 mm

## FITTING

Fitting type	Rectangular plate
Plate length	95 mm
Plate width	70 mm
Plate hole length (Minimum)	45 mm
Plate hole length (Maximum)	52 mm
Plate hole width (Minimum)	66.5 mm
Plate hole width (Maximum)	77 mm
Plate hole diameter	8 mm

# ALPHA LIGHT

3430POO065P60-95X70

EAN 4031582303339  
Order number 10000285



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

