

ALPHA LIGHT

3438POO065P60-95X54

EAN 4031582303346
Order number 00010798



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Alpha light |
| Housing type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 120 kg |
| Load capacity Static | 240 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 83 mm |
| Overall width | 54 mm |
| Overall weight | 0.234 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polypropylene |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 65 mm |
| Tread width | 30 mm |
| Body width | 30 mm |
| Hardness of tread (D) | 65 Shore D |

HOUSING

| | |
|---------------|--------------------|
| Material | Steel sheet, heavy |
| Fork shape | Broad |
| Colour | Blue passivated |
| Dome diameter | 54 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 95 mm |
| Plate width | 54 mm |
| Plate hole length (Maximum) | 24 mm |
| Plate hole width (Maximum) | 71 mm |
| Plate hole diameter | 9 mm |

ALPHA LIGHT

3438POO065P60-95X54

EAN 4031582303346
Order number 00010798



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

