

ALPHA LIGHT

3438POO065P60-95X54

EAN 4031582303346
Order number 00010798



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Alpha light
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	264.55 lb
Load capacity Static	529.11 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	3.27 in
Overall width	2.13 in
Overall weight	0.52 lb

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	1.18 in
Body width	1.18 in
Hardness of tread (D)	65 Shore D

HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Color	Blue passivated
Dome diameter	2.13 in

FITTING

Fitting type	Rectangular plate
Plate length	3.74 in
Plate width	2.13 in
Plate hole length (Maximum)	0.94 in
Plate hole width (Maximum)	2.8 in
Plate hole diameter	0.35 in

ALPHA LIGHT

3438POO065P60-95X54

EAN 4031582303346
Order number 00010798



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

