

COMPACTA

1298UOI014P80-26

EAN 4031582300024
Order number 00021119



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Housing type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	15 kg
Load capacity Static	30 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	13.5 mm
Overall width	19 mm
Overall weight	0.008 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	14 mm
Tread width	14 mm
Body width	14 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material	Steel sheet, light
Fork shape	Straight
Colour	Blue passivated
Dome diameter	19 mm

FITTING

Fitting type	Round plate
Plate hole length (Maximum)	20 mm
Plate hole width (Maximum)	20 mm
Plate hole diameter	2.5 mm

COMPACTA

1298UOI014P80-26

EAN 4031582300024
Order number 00021119



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

