

COMPACTA

2198UOI030P60-45X20

EAN 4031582030068
Order number 00021134



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Compacta
Housing type	Fixed castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	66.14 lb
Load capacity Static	132.28 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall height	1.34 in
Overall width	0.79 in
Overall weight	0.07 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	1.18 in
Tread width	0.59 in
Body width	0.59 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Steel sheet, medium
Fork shape	Angular
Color	Blue passivated
Dome diameter	0.79 in

FITTING

Fitting type	Rectangular plate
Plate length	1.77 in
Plate width	0.79 in
Plate hole length (Maximum)	1.38 in
Plate hole width (Maximum)	1.38 in
Plate hole diameter	0.22 in

COMPACTA

2198UOI030P60-45X20

EAN 4031582030068
Order number 00021134



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

