

# ALPHA LIGHT

3430POI058P60-80X60

EAN 4031582303322  
Order number 00022164



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha light
Housing type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	76 mm
Overall width	50 mm
Overall weight	0.269 kg

## WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Screwed with nut
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	58 mm
Tread width	28 mm
Body width	28 mm
Hardness of tread (D)	65 Shore D

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	One ball race
Colour	Blue passivated
Offset	21 mm
Swivel radius	50 mm
Swivel interference	100 mm
Dome diameter	50.5 mm

## FITTING

Fitting type	Rectangular plate
Plate length	80 mm
Plate width	60 mm
Plate hole length (Maximum)	40 mm
Plate hole width (Maximum)	60 mm
Plate hole diameter	7.5 mm

# ALPHA LIGHT

3430POI058P60-80X60

EAN 4031582303322  
Order number 00022164



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

