

# ALPHA

3478UOO200P63

EAN 4031582030143  
Order number 00028480



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	771.62 lb
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	9.45 in
Overall width	4.53 in
Overall weight	4.07 lb

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Color	Blue passivated

## FITTING

Fitting type	Rectangular plate
Plate length	5.51 in
Plate width	4.53 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

# ALPHA

3478UOO200P63

EAN 4031582030143  
Order number 00028480



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

