

# ALPHA

3477PVR200P30-13

EAN 4031582305739  
Order number 00030483



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	440.92 lb
Load capacity Static	881.85 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	9.25 in
Overall width	3.78 in
Overall weight	6.52 lb

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Axle	Screwed with nut
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	2.17 in
Swivel radius	6.57 in
Swivel interference	13.15 in
Dome diameter	3.78 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

# ALPHA

3477PVR200P30-13

EAN 4031582305739  
Order number 00030483



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

