

# ALPHA

3472PVR200P63

EAN 4031582304923  
Order number 00030718



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Alpha
Housing type	Swivel castor with total lock, head end of castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	451.95 lb
Load capacity Static	903.89 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	9.45 in
Overall width	3.78 in
Overall weight	6.72 lb

## WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Axle	Screwed with nut
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	7.87 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	80 Shore A

## HOUSING

Material	Steel sheet, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	2.17 in
Swivel radius	6.1 in
Swivel interference	12.2 in
Dome diameter	3.78 in

## FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

# ALPHA

3472PVR200P63

EAN 4031582304923  
Order number 00030718



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

