

STORA

3875ZJJ160P30-13 R

EAN 4031582307764
Order number 00030743



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor with wheel brake
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	7.32 in
Overall width	3.78 in
Overall weight	4.19 lb

WHEEL

Body material	Flanged wheel
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Axle	Screwed with nut
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	6.3 in
Tread width	1.57 in
Body width	1.57 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, heavy
Fork shape	Special Function
Swivel bearing	Two ball races
Color	Blue passivated
Offset	2.17 in
Swivel radius	5.31 in
Swivel interference	10.63 in
Dome diameter	3.78 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

ADDITIONAL INFORMATION

Designed for the following palletsize: track width: approx. 2,75 mm, groove width: approx. 5,7 mm, groove depth: > 10 mm.

STORA

3875ZJJ160P30-13 R

EAN 4031582307764
Order number 00030743



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

