

INTEGRAL TWIN

2946UAP100R26-28S45 D 9002 4XM8

EAN 4031582302585
Order number 00039764



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Integral twin |
| Housing type | Swivel castor with central , total lock |
| Standard | EN12531 - Hospital Bed Castors |
| Load capacity at 3 km/h | 275.58 lb |
| Load capacity at 4 km/h | 275.58 lb |
| Load capacity Static | 826.73 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 5.08 in |
| Overall width | 2.48 in |
| Overall weight | 2.31 lb |
| Certification | Tested and monitored by TÜV Süd |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Wheel color | Gray white (RAL9002) |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 0.59 in |
| Body width | 0.59 in |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material | Steel sheet, medium |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Color | Gray white (RAL9002) |
| Offset | 1.22 in |
| Swivel radius | 3.35 in |
| Swivel interference | 6.69 in |
| Dome diameter | 2.42 in |

FITTING

| | |
|------------------------------|-------------------------------------|
| Fitting type | Stem with cam hole for profile bars |
| Bolt diameter | 1.1 in |
| Bolt length | 3.78 in |
| Bolt thread position | 0.75 in |
| Bolt mounting holes quantity | 4 |

INTEGRAL TWIN

2946UAP100R26-28S45 D 9002 4XM8

EAN 4031582302585
Order number 00039764



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

