

ALPHA STAINLESS

8477UOO080P30-13

EAN 4031582313062
Order number 00061967



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	330.69 lb
Load capacity Static	661.39 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall height	4.25 in
Overall width	2.95 in
Overall weight	1.54 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.15 in
Tread width	1.34 in
Body width	1.34 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Color	Stainless steel
Offset	1.75 in
Swivel radius	4.84 in
Swivel interference	9.69 in
Dome diameter	2.95 in
Stainless	✓

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

ALPHA STAINLESS

8477UOO080P30-13

EAN 4031582313062
Order number 00061967



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

