

# ALPHA STAINLESS

8477UOO125P30-13

EAN 4031582313109  
Order number 00062126



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	200 kg
Load capacity Static	400 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	155 mm
Overall width	75 mm
Overall weight	0.907 kg

## WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	125 mm
Tread width	40 mm
Body width	40 mm
Hardness of tread (D)	75 Shore D

## HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	40 mm
Swivel radius	123 mm
Swivel interference	246 mm
Dome diameter	75 mm
Stainless	✓

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

# ALPHA STAINLESS

8477UOO125P30-13

EAN 4031582313109  
Order number 00062126



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

