

STORA

2370PJP125P30-13 2.0

EAN 4031582300369
Order number 00064846



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	155 mm
Overall width	60 mm
Overall weight	0.583 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	83 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	38 mm
Swivel radius	100.5 mm
Swivel interference	201 mm
Dome diameter	60 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

STORA

2370PJP125P30-13 2.0

EAN 4031582300369
Order number 00064846

TECHNICAL DRAWINGS

