

STYLEA

5925UOI075L51-10D20 9011/9011/9011

EAN 4031582311242
Order number 00078133



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Stylea |
| Housing type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 110.23 lb |
| Load capacity Static | 220.46 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 140 °F |
| Overall height | 3.03 in |
| Overall width | 2.13 in |
| Overall weight | 0.28 lb |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Tread color | Graphite black (RAL9011) |
| Wheel color | Graphite black (RAL9011) |
| Threadguards | Without threadguard |
| Diameter | 2.95 in |
| Tread width | 0.31 in |
| Body width | 0.31 in |
| Hardness of tread (D) | 65 Shore D |

HOUSING

| | |
|---------------------|--------------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Color | Graphite black (RAL9011) |
| Offset | 1.18 in |
| Swivel radius | 3.43 in |
| Swivel interference | 6.85 in |
| Dome diameter | 0.79 in |

FITTING

| | |
|--------------------|----------------------------|
| Fitting type | Blind hole for B10 fitting |
| Bolt hole diameter | 0.39 in |

PRODUCT INFORMATION

STYLEA

5925UOI075L51-10D20 9011/9011/9011

EAN 4031582311242
Order number 00078133



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

