

# OMIKRON TWIN

9958FTP250P68

EAN 4031582316995  
Order number 00801115



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                       |
|-----------------------------|---------------------------------------|
| Product name                | Omikron twin                          |
| Housing type                | Fixed castor                          |
| Standard                    | similar EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 5000 kg                               |
| Load capacity at 6 km/h     | 3600 kg                               |
| Load capacity Static        | 7500 kg                               |
| Temperature range (Minimum) | -10 °C                                |
| Temperature range (Maximum) | 60 °C                                 |
| Overall height              | 365 mm                                |
| Overall width               | 272 mm                                |
| Overall weight              | 38.319 kg                             |

## WHEEL

|                       |                        |
|-----------------------|------------------------|
| Body material         | Casting                |
| Tread material        | Polyurethane, casted   |
| Bearing               | Precision ball bearing |
| Axle                  | Screwed with nut       |
| Wheel color           | Honey yellow (RAL1005) |
| Threadguards          | With threadguard       |
| Diameter              | 250 mm                 |
| Tread width           | 80 mm                  |
| Body width            | 80 mm                  |
| Hardness of tread (A) | 92 Shore A             |
| Hardness of tread (D) | 42 Shore D             |

## HOUSING

|               |                                  |
|---------------|----------------------------------|
| Material      | Cast iron, or iron forged, heavy |
| Fork shape    | Twin wheel housing               |
| Colour        | Transparent coating              |
| Dome diameter | 235 mm                           |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 270 mm            |
| Plate width                 | 250 mm            |
| Plate hole length (Maximum) | 210 mm            |
| Plate hole width (Maximum)  | 230 mm            |
| Plate hole diameter         | 17 mm             |

# OMIKRON TWIN

9958FTP250P68

EAN 4031582316995  
Order number 00801115



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

