

# OMIKRON

9258FTP250P65

EAN 4031582314076  
Order number 00803581



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

### PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

### CORE ATTRIBUTES

Product name	Omikron
Housing type	Fixed castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	3000 kg
Load capacity at 6 km/h	2200 kg
Load capacity Static	4500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	325 mm
Overall width	182 mm
Overall weight	23.128 kg

### WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	250 mm
Tread width	100 mm
Body width	100 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

### HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Straight
Colour	Transparent coating
Dome diameter	160 mm

### FITTING

Fitting type	Rectangular plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	160 mm
Plate hole diameter	15 mm

## TECHNICAL DRAWINGS

