

# OMIKRON TWIN

9950FTP150P65

EAN 4031582316766  
Order number 00803669



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Omikron twin
Housing type	Swivel castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	1800 kg
Load capacity at 6 km/h	1400 kg
Load capacity Static	2700 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	230 mm
Overall width	189 mm
Overall weight	17.825 kg

## WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	150 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Colour	Transparent coating
Offset	55 mm
Swivel radius	141 mm
Swivel interference	282 mm
Dome diameter	160 mm

## FITTING

Fitting type	Rectangular plate
Plate length	200 mm
Plate width	160 mm
Plate hole length (Maximum)	120 mm
Plate hole width (Maximum)	160 mm
Plate hole diameter	15 mm

# OMIKRON TWIN

9950FTP150P65

EAN 4031582316766  
Order number 00803669



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

