

KAPPA

9682ITP250P63 CL67

EAN 4031582315974
Order number 00827807



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Kappa |
| Housing type | Swivel castor with total lock, head end of castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 1000 kg |
| Load capacity at 6 km/h | 800 kg |
| Load capacity Static | 2000 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 305 mm |
| Overall width | 116 mm |
| Overall weight | 5.925 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Aluminium |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 250 mm |
| Tread width | 55 mm |
| Body width | 55 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|---|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races, reinforced or stainless |
| Colour | Blue passivated |
| Offset | 61 mm |
| Swivel radius | 187.5 mm |
| Swivel interference | 375 mm |
| Dome diameter | 111 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 135 mm |
| Plate width | 110 mm |
| Plate hole length (Minimum) | 75 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 105 mm |
| Plate hole diameter | 11 mm |

KAPPA

9682ITP250P63 CL67

EAN 4031582315974
Order number 00827807



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

