

KAPPA LOAD

9651TOP150P63 CL67

EAN 4031582314656
Order number 00829959



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Kappa load |
| Housing type | Swivel castor with directional lock |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 960 kg |
| Load capacity at 6 km/h | 800 kg |
| Load capacity Static | 1600 kg |
| Temperature range (Minimum) | -30 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 200 mm |
| Overall width | 110 mm |
| Overall weight | 4.384 kg |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Natural white |
| Threadguards | With threadguard |
| Diameter | 150 mm |
| Tread width | 50 mm |
| Body width | 50 mm |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|--|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Deep-groove ball thrust roller bearing |
| Colour | Blue passivated |
| Offset | 58 mm |
| Swivel radius | 137.5 mm |
| Swivel interference | 275 mm |
| Dome diameter | 111 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 135 mm |
| Plate width | 110 mm |
| Plate hole length (Minimum) | 75 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 105 mm |
| Plate hole diameter | 11 mm |

KAPPA LOAD

9651TOP150P63 CL67

EAN 4031582314656
Order number 00829959



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

