

ZETA

4681IEP125P63

EAN 4031582307931
Order number 00830070



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Zeta
Housing type	Swivel castor with directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	661.39 lb
Load capacity at 6 km/h	529.11 lb
Load capacity Static	1322.77 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	6.46 in
Overall width	3.78 in
Overall weight	6.48 lb

WHEEL

Body material	Aluminum
Tread material	Elastic tire, black, vulcanized
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.97 in
Body width	1.97 in
Hardness of tread (A)	67 Shore A

HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Color	Blue passivated
Offset	2.17 in
Swivel interference	9.06 in
Dome diameter	3.78 in

FITTING

Fitting type	Rectangular plate
Plate length	5.39 in
Plate width	4.13 in
Plate hole length (Minimum)	2.95 in
Plate hole length (Maximum)	3.15 in
Plate hole width (Minimum)	2.95 in
Plate hole width (Maximum)	4.13 in
Plate hole diameter	0.43 in

ZETA

4681IEP125P63

EAN 4031582307931
Order number 00830070



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

