

ZETA

4688UOO200P63 WH-W46

EAN 4031582308341
Order number 00830083



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Zeta
Housing type	Fixed castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	480 kg
Load capacity Static	1200 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall height	240 mm
Overall width	117 mm
Overall weight	1.808 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	200 mm
Tread width	46 mm
Body width	46 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material	Steel sheet, very heavy
Fork shape	Broad, reinforced
Colour	Blue passivated

FITTING

Fitting type	Rectangular plate
Plate length	137 mm
Plate width	117 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

ZETA

4688UOO200P63 WH-W46

EAN 4031582308341
Order number 00830083



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

