

OMIKRON

9258FTP300P66

EAN 4031582314090
Order number 00830233



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Omikron
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	3120 kg
Load capacity at 6 km/h	2600 kg
Load capacity Static	6240 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	370 mm
Overall width	182 mm
Overall weight	32.749 kg

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	300 mm
Tread width	100 mm
Body width	100 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Straight
Colour	Transparent coating
Dome diameter	160 mm

FITTING

Fitting type	Rectangular plate
Plate length	250 mm
Plate width	200 mm
Plate hole length (Maximum)	160 mm
Plate hole width (Maximum)	210 mm
Plate hole diameter	17 mm

TECHNICAL DRAWINGS

