

# OMIKRON

9258FTP300P66

EAN 4031582314090  
Order number 00830233



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Omikron
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	6878.41 lb
Load capacity at 6 km/h	5732.01 lb
Load capacity Static	13756.83 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	140 °F
Overall height	14.57 in
Overall width	7.17 in
Overall weight	72.2 lb

## WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	11.81 in
Tread width	3.94 in
Body width	3.94 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Straight
Color	Transparent coating
Dome diameter	6.3 in

## FITTING

Fitting type	Rectangular plate
Plate length	9.84 in
Plate width	7.87 in
Plate hole length (Maximum)	6.3 in
Plate hole width (Maximum)	8.27 in
Plate hole diameter	0.67 in

## TECHNICAL DRAWINGS

