

KAPPA LOAD

9652FTP160P63 CL67

EAN 4031582314717
Order number 00830393



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Swivel castor with total lock, head end of castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	900 kg
Load capacity at 6 km/h	750 kg
Load capacity Static	1500 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	205 mm
Overall width	116 mm
Overall weight	6.281 kg

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	160 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Colour	Blue passivated
Offset	58 mm
Swivel radius	140 mm
Swivel interference	280 mm
Dome diameter	111 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA LOAD

9652FTP160P63 CL67

EAN 4031582314717
Order number 00830393



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

