

KAPPA

9680IEP160P63 CL67

EAN 4031582315141
Order number 00830411



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Kappa |
| Housing type | Swivel castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 771.62 lb |
| Load capacity at 6 km/h | 617.29 lb |
| Load capacity Static | 1543.23 lb |
| Temperature range (Minimum) | -4 °F |
| Temperature range (Maximum) | 185 °F |
| Overall height | 8.07 in |
| Overall width | 4.33 in |
| Overall weight | 9.12 lb |

WHEEL

| | |
|-----------------------|---------------------------------|
| Body material | Aluminum |
| Tread material | Elastic tire, black, vulcanized |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Jet black (similar RAL9005) |
| Threadguards | With threadguard |
| Diameter | 6.3 in |
| Tread width | 1.97 in |
| Body width | 1.97 in |
| Hardness of tread (A) | 68 Shore A |

HOUSING

| | |
|---------------------|---|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races, reinforced or stainless |
| Color | Blue passivated |
| Offset | 2.28 in |
| Swivel radius | 5.51 in |
| Swivel interference | 11.02 in |
| Dome diameter | 4.37 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 5.31 in |
| Plate width | 4.33 in |
| Plate hole length (Minimum) | 2.95 in |
| Plate hole length (Maximum) | 3.15 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 4.13 in |
| Plate hole diameter | 0.43 in |

TECHNICAL DRAWINGS

