

KAPPA LOAD

9651FTP200P64 CL97

EAN 4031582314489
Order number 00863070



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------------|
| Product name | Kappa load |
| Housing type | Swivel castor with directional lock |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 4 km/h | 1680 kg |
| Load capacity at 6 km/h | 1400 kg |
| Load capacity Static | 2800 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 60 °C |
| Overall height | 255 mm |
| Overall width | 140 mm |
| Overall weight | 13.376 kg |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Casting |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Honey yellow (RAL1005) |
| Threadguards | With threadguard |
| Diameter | 200 mm |
| Tread width | 80 mm |
| Body width | 80 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|----------------------------------------|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Deep-groove ball thrust roller bearing |
| Colour | Zink-iron (transparent) |
| Offset | 65 mm |
| Swivel radius | 170 mm |
| Swivel interference | 340 mm |
| Dome diameter | 140 mm |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 175 mm |
| Plate width | 140 mm |
| Plate hole length (Maximum) | 105 mm |
| Plate hole width (Maximum) | 140 mm |
| Plate hole diameter | 15 mm |

KAPPA LOAD

9651FTP200P64 CL97

EAN 4031582314489
Order number 00863070



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

