

MAXTECH

UAP125X32-Ø8

EAN4031582322941

Order number00027145



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Product type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	160 kg
Load capacity Static	320 kg
Temperature range (Minimum)	-25 °C
Temperature range (Maximum)	80 °C
Overall weight	0.356 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Axle hole diameter	8.3 mm
Hub length	36.5 mm
Hardness of tread (D)	40 Shore D

MAXTECH

UAP125X32-Ø8

EAN
Order number

4031582322941
00027145

TECHNICAL DRAWINGS

