

PRODUCT INFORMATION

MAXTECH

UAP125X32-Ø8

EAN
Order number

4031582322941
00027145



Image may differ from the original product

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Axle hole diameter | 0.33 in |
| Hub length | 1.44 in |
| Hardness of tread (D) | 40 Shore D |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Maxtech |
| Product type | Wheel |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 352.74 lb |
| Load capacity Static | 705.48 lb |
| Temperature range (Minimum) | -13 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 0.78 lb |

PRODUCT INFORMATION

MAXTECH

UAP125X32-Ø8

EAN
Order number

4031582322941
00027145

TECHNICAL DRAWINGS

