

INTEGRAL

2044UAP125R36-32S30 D 9002 4XM6

EAN 4031582300178
Broj porudžbine 00039275



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

| | |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ○ ○ |
| Buka u pokretu | ● ● ● ○ ○ |
| Ishrana | ● ● ● ● ○ |
| otpornost na rdju | ● ● ● ○ ○ |

OSNOVNI ATRIBUTI

| | |
|--------------------------------|---|
| Naziv proizvoda | Integral |
| Tip kućišta | Okreni Tocak sa centralnom, totalnom ili usmerena kocnica |
| Standard | EN12531 - Bolnički stolovi |
| Nosivost na 3 km/h | 150 kg |
| Nosivost na 4 km/h | 150 kg |
| Statički Nosivost | 450 kg |
| Temperaturni opseg (Minimalno) | -25 °C |
| Opseg temperature (maksimalni) | 80 °C |
| Sveukupna visina | 158 mm |
| Ukupna širina | 62 mm |
| Ukupna težina | 0,976 kg |
| Sertifikacija | Ispitano i nadgledano od strane TÜV Süd |

TOCAK

| | |
|----------------------------|--------------------------|
| Materijal za telo | poliamid |
| materijal omotaca | Poliuretan, liveno |
| Nošenje | precizini kuglicni lezaj |
| Boja omotac | Slat siva (RAL7015) |
| Boja Tocak | Slat siva (RAL7015) |
| stitnici omotaca | Integrisani threadguard |
| Prečnik | 125 mm |
| Širina omotac | 32 mm |
| Širina tela | 32 mm |
| Teškoća gazećeg omotac (A) | 92 Šor A |
| Teškoća gazećeg omotac (D) | 42 Šor D |

KUCISTE

| | |
|-----------------|--------------------------|
| Materijal | Čelični list, srednji |
| oblik viljuska | Zatvoreno |
| okretni lezaj | precizini kuglicni lezaj |
| Boja | Siva bela (RAL9002) |
| ofset | 35 mm |
| okretni radijus | 97,5 mm |
| Otpor okretanju | 195 mm |
| Prečnik kupole | 62 mm |

PRILAGOĐAVANJE

| | |
|------------------------------------|--|
| Tip uklapanja | stablo sa bregasta rupa za trake profila, kratka Verzija |
| Prečnik sraf | 32 mm |
| Dužina sraf | 51 mm |
| Položaj sraf | 7 mm |
| Količina otvora za montiranje sraf | 4 |



IF nagrada za
Dizajn



Red Dot Dizajn
Award

INTEGRAL



2044UAP125R36-32S30 D 9002 4XM6

EAN 4031582300178
Broj porudžbine 00039275



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI



IF nagrada za
Dizajn



Red Dot Dizajn
Award