

# AGILA

2447UAP125R05-28

EAN 4031582300567

Swivel caster with total lock, trailing end of caster, housing made of pressed steel, bright zinc plated, blue passivated, covered precision swivel bearing, hardened balls and tracks, bearing sleeve welded to fork, wheel axle with nut, solid plug fitting. Wheel center made of Polyamide, Tread: Polyurethane, precision ball bearing , with threadguards



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

## Technical Data

Wheel diameter	125 mm
Wheel width	32 mm
Bolt-Ø	28 mm
Bolt length	45 mm
Offset	43 mm
Swivel Interference	211 mm
Overall height	170 mm
Temperature	- 40 / + 80 °C
Standard	EN 12530
Weight	1.375 kg
Hardness of tread	Shore D 40
Load capacity (dynamic)	150 kg
Load capacity (static)	300 kg

## Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○