

INTEGRAL TWIN

3944UAP150R36-32S30

EAN 4031582355079

Swivel castor with central, total lock and central directional lock, frame made of pressed steel, precision ball bearing in swivel head, housing with synthetic cover, stem with cam hole for profile bars, short version. Wheel centre made of Polyamide, Tread: Polyurethane, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product

Technical Data

Wheel diameter	150 mm
Wheel width	15 mm
Castor width	74 mm
Bolt-Ø	32 mm
Bolt length	51 mm
Dome-Ø	70 mm
Offset	45 mm
Swivel Interference	249 mm
Overall height	193 mm
Temperature	- 25 / - 25 °C
Standard	EN 12531
Weight	2.226 kg
Swivel Radius	124.5 mm
Hardness of tread	Shore D 40
Load capacity	250 kg
Load capacity (static)	750 kg

Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○