

PRODUCT INFORMATION

KAPPA

9680ITP100P63 FLAT

EAN
Order number

4031582315172
00802068



Image may differ from the original product

PERFORMANCE

Roll performance	●●●●○
Movement noise	●●●○●
Attrition	●●●●○
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Kappa
Product type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	540 kg
Load capacity at 6 km/h	430 kg
Load capacity Static	1080 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	145 mm
Overall width	110 mm
Overall weight	3.401 kg

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	100 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	41 mm
Swivel radius	95 mm
Swivel interference	190 mm
Dome diameter	111 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

KAPPA

9680ITP100P63 FLAT

EAN
Order number

4031582315172
00802068

TECHNICAL DRAWINGS

