

AGILA

2475DIK050B10-11X31

EAN 4031582301687
Order number 00006927



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	88.18 lb
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	2.83 in
Overall weight	0.56 lb

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, non-marking
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.75 in
Hardness of tread (A)	80 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	0.94 in

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

AGILA

2475DIK050B10-11X31

EAN 4031582301687
Order number 00006927



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

