

AGILA

2470PJP100R05-28

EAN 4031582300932
Order number 00028310



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	138 mm
Overall weight	0.848 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm

FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm

AGILA

2470PJP100R05-28

EAN 4031582300932
Order number 00028310



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

