

# AGILA CARE US

2447JFX125R05-28

EAN 4031582300543



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila care US                 |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 150 kg                        |
| Load capacity Static        | 300 kg                        |
| Temperature range (Minimum) | -20 °C                        |
| Temperature range (Maximum) | 85 °C                         |
| Overall height              | 170 mm                        |
| Overall weight              | 1.547 kg                      |

## WHEEL

|                       |                                       |
|-----------------------|---------------------------------------|
| Body material         | Zinc die-cast                         |
| Tread material        | Elastic tire, non-marking, vulcanized |
| Bearing               | Precision ball bearing, sealed        |
| Threadguards          | With threadguard                      |
| Diameter              | 125 mm                                |
| Tread width           | 32 mm                                 |
| Hardness of tread (A) | 75 Shore A                            |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material            | Steel sheet, medium    |
| Fork shape          | Broad                  |
| Swivel bearing      | Precision ball bearing |
| Offset              | 43 mm                  |
| Swivel interference | 211 mm                 |
| Electric conductive | ✓                      |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 28 mm             |
| Bolt length   | 45 mm             |