

KAPPA

9680FTP250P64

EAN 4031582315080
Order number 00802244



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	2160 kg
Load capacity at 6 km/h	1800 kg
Load capacity Static	3600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	305 mm
Overall weight	20.134 kg

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	250 mm
Tread width	80 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	65 mm
Swivel radius	190 mm
Swivel interference	380 mm

FITTING

Fitting type	Rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	140 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	15 mm

KAPPA

9680FTP250P64

EAN 4031582315080
Order number 00802244



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

