

KAPPA

9680TOO150P63

EAN 4031582315257
Order number 00802949



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	960 kg
Load capacity at 6 km/h	800 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	200 mm
Overall weight	3.687 kg

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	150 mm
Tread width	50 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	58 mm
Swivel radius	133 mm
Swivel interference	266 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

KAPPA

9680TOO150P63

EAN 4031582315257
Order number 00802949



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

