

AGILA CARE US

2440UAP125R05-28

EAN 4031582387315



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---------------------------|
| Product name | Agila care US |
| Housing type | Swivel castor |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 330.69 lb |
| Load capacity Static | 661.39 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 6.69 in |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 4.92 in |
| Tread width | 1.26 in |
| Hardness of tread (D) | 40 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material | Steel sheet, medium |
| Fork shape | Broad |
| Swivel bearing | Precision ball bearing |
| Offset | 1.69 in |
| Swivel radius | 4.15 in |
| Swivel interference | 8.31 in |

FITTING

| | |
|---------------|-------------------|
| Fitting type | Solid stem, round |
| Bolt diameter | 1.1 in |
| Bolt length | 1.77 in |