

ALPHA STAINLESS

8477UFC100P30-13

EAN 4031582422528



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Housing type	Swivel castor with total lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	150 kg
Load capacity Static	300 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall height	128 mm
Overall weight	0.925 kg

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing, stainless
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	100 mm
Tread width	34 mm
Hardness of tread (A)	64 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Offset	41 mm
Swivel interference	242 mm
Stainless	✓

FITTING

Fitting type	Bolt hole
Bolt hole diameter	13 mm

ALPHA STAINLESS

8477UFC100P30-13

EAN 4031582422528



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

