

E-DRIVE OPTIMA

EDOAUFF125P60

EAN 4031582497885



BETTER MOBILITY. BETTER LIFE.

E-Drive optima, drive unit with integrated control unit, can be lowered and raised, brushless motor with deceleration function and constant torque. Solid housing made of galvanized sheet steel, the wheel can be replaced by the customer and ordered individually, maintenance-free.



Picture may differ from original product


기술 데이터

휠	UFF, solid rubber, non-marking, Shore 63A
휠 직경	125 mm
휠 폭	35 mm
설치 높이	170 mm
길이	max. 315 mm (Emergency release activated)
비상 정지 버튼	기계식 작동
폭	220 mm
작동 모터	24 V DC
작동 방향	전진/후진
높이 (접혔을 때)	140 mm
바닥 허용 편차	+/- 20 mm
최대 턱 넘이 높이	15 mm
최대 인양력	400 N
무게	7.25 kg


작동 모터

전압	18 V DC
토크	1 Nm
출력	260 W
RPM	2100 rpm
전류	12.1 A

Dimensions



Structure & Mounting



E-DRIVE OPTIMA

EDOAUFF125P60

EAN 4031582497885



BETTER MOBILITY. BETTER LIFE.

작동방식	S1
최대 속도	6 km/h

출력장치

전압	24 V DC
토크	4 Nm
출력	14.8 W
RPM	35.3 min/ ⁻¹
전류	3.5 A
작동방식	주기적인 S3
사용 환경	Operating temperature 5 to 50° C (recommended 15 to 50° C), humidity 90%, non-condensing
허용 보관온도	-10 bis +40 °C
방수 등급 Třída ochrany	IPX4 방수 (드라이브 유닛 또는 플러그 부위에 튀는 물 방수)

Advantages at a glance

롤 저항성	● ● ● ● ●
이동 소음	● ● ● ○ ○
마찰	● ● ● ○ ○
부식 방지	● ● ● ○ ○