

NOVATECH

STP500x150-Ø50 HL160

EAN 4031582322286

Wheel centre made of pressed steel, lacquered, heavy duty, Tread: Polyurethane, casted, precision ball bearing



BETTER MOBILITY. BETTER LIFE.




Picture may differ from original product

Technical Data

Wheel diameter	500 mm
Wheel width	150 mm
Axle Hole-Ø	50 mm
Hub length	160 mm
Temperature	- 10 / + 60 °C
Standard	EN 12533
Weight	62.353 kg
Hardness of tread	Shore D 42
Load capacity	5300 kg
Load capacity (static)	10600 kg

Dimensions



Advantages at a glance

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

Structure & Mounting

