

## NOVATECH

STP 500X150-Ø50 HL160

EAN 4031582322286

Broj porudžbine 00803302



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik od limova, težak
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Med žuta (RAL1005)
stitnici omotaca	Sa threadguard
Prečnik	500 mm
Širina omotac	150 mm
dimenzija rupa osovina	50 mm
dužina glavcine	160 mm
Širina tela	150 mm
Teškoća gazećeg omotac (A)	92 Šor A
Teškoća gazećeg omotac (D)	42 Šor D

## PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Standard	EN12533 - Tockovi za teske terete
Nosivost na 4 km/h	6360 kg
Nosivost na 6 km/h	5300 kg
Statički Nosivost	10600 kg
Temperaturni opseg (Minimalno)	-10 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	62,353 kg

# NOVATECH

STP 500X150-Ø50 HL160

EAN 4031582322286

Broj porudžbine 00803302



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

