

AGILA TWIN

2970UOO050P30-11

EAN 4031582302769
Order number 00030048



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall height	2.72 in
Overall width	2.09 in
Overall weight	0.41 lb

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing
Wheel color	Slate gray (RAL7015)
Threadguards	Without threadguard
Diameter	1.97 in
Tread width	0.79 in
Body width	0.79 in
Hardness of tread (D)	75 Shore D

HOUSING

Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.98 in
Swivel radius	2.09 in
Swivel interference	4.17 in
Dome diameter	2.09 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.43 in

AGILA TWIN

2970UOO050P30-11

EAN 4031582302769
Order number 00030048



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

