

# AGILA TWIN

2975UAK050P40

EAN 4031582302837  
Order number 00031002



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila twin
Housing type	Swivel castor with wheel brake
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	154.32 lb
Load capacity Static	308.65 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	176 °F
Overall height	2.72 in
Overall width	2.24 in
Overall weight	0.78 lb

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Cone ball bearing
Wheel color	Slate gray (RAL7015)
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.79 in
Body width	0.79 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

## HOUSING

Material	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.98 in
Swivel radius	3.03 in
Swivel interference	6.1 in
Dome diameter	2.09 in

## FITTING

Fitting type	Square plate
Plate length	2.36 in
Plate width	2.36 in
Plate hole length (Minimum)	1.5 in
Plate hole length (Maximum)	1.89 in
Plate hole width (Minimum)	1.5 in
Plate hole width (Maximum)	1.89 in
Plate hole diameter	0.25 in

# AGILA TWIN

2975UAK050P40

EAN 4031582302837  
Order number 00031002



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

