

INTEGRAL

2044UAP150R26-28S45 D 9002 4XM8

EAN 4031582300185
Order number 00061434



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Integral |
| Housing type | Swivel castor with central, total or directional lock |
| Standard | EN12531 - Hospital Bed Castors |
| Load capacity at 3 km/h | 150 kg |
| Load capacity at 4 km/h | 150 kg |
| Load capacity Static | 450 kg |
| Temperature range (Minimum) | -25 °C |
| Temperature range (Maximum) | 80 °C |
| Overall height | 183 mm |
| Overall width | 62 mm |
| Overall weight | 0.99 kg |
| Certification | Tested and monitored by TÜV Süd |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Tread color | Slate grey (RAL7015) |
| Wheel color | Slate grey (RAL7015) |
| Threadguards | Integrated threadguard |
| Diameter | 150 mm |
| Tread width | 32 mm |
| Body width | 32 mm |
| Hardness of tread (A) | 92 Shore A |
| Hardness of tread (D) | 42 Shore D |

HOUSING

| | |
|---------------------|------------------------|
| Material | Steel sheet, medium |
| Fork shape | Closed |
| Swivel bearing | Precision ball bearing |
| Colour | Grey white (RAL9002) |
| Offset | 40 mm |
| Swivel radius | 115 mm |
| Swivel interference | 230 mm |
| Dome diameter | 62 mm |

FITTING

| | |
|------------------------------|-------------------------------------|
| Fitting type | Stem with cam hole for profile bars |
| Bolt diameter | 28 mm |
| Bolt length | 96 mm |
| Bolt thread position | 19 mm |
| Bolt mounting holes quantity | 4 |



IF
Design
Award



Red Dot
Design
Award

INTEGRAL

2044UAP150R26-28S45 D 9002 4XM8

EAN 4031582300185
Order number 00061434



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

