

STYLEA

5925UOI075L51-10D20 9011/9011/9011

EAN 4031582311242
Order number 00078133



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	77 mm
Overall width	54 mm
Overall weight	0.128 kg

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm
Body width	8 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	Graphite black (RAL9011)
Offset	30 mm
Swivel radius	87 mm
Swivel interference	174 mm
Dome diameter	20 mm

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm

PRODUCT INFORMATION

STYLEA

5925UOI075L51-10D20 9011/9011/9011

EAN 4031582311242
Order number 00078133



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

