

OMIKRON TWIN

9950STP500P68

EAN 4031582316858
Order number 00801528



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Omikron twin
Housing type	Swivel castor
Standard	similar EN12532 - Transport Equipment
Load capacity at 4 km/h	8500 kg
Load capacity at 6 km/h	6000 kg
Load capacity Static	12750 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	610 mm
Overall width	345 mm
Overall weight	125.425 kg

WHEEL

Body material	Sheet steel, heavy
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	500 mm
Tread width	80 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Deep-groove ball thrust roller bearing
Colour	Transparent coating
Offset	130 mm
Swivel radius	395 mm
Swivel interference	790 mm
Dome diameter	316 mm

FITTING

Fitting type	Rectangular plate
Plate length	270 mm
Plate width	250 mm
Plate hole length (Maximum)	210 mm
Plate hole width (Maximum)	230 mm
Plate hole diameter	17 mm

OMIKRON TWIN

9950STP500P68

EAN 4031582316858
Order number 00801528



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

